

BACK-ROLLER BLACK'N WHITE

Rear pannier (pair) in colour combination black/black or white/black



Additional fastening with strap, buckle and D-ring

QL2.1 system

IP 64

Buckles for closing the rolling closure at the top or for attaching the shoulder strap

PD62

PS60

Two lateral 3M Scotchlite reflectors

anti scratch

PVC free

Shoulder strap with padding, serves as compression strap



Release handle for mounting and releasing the QL2.1 system

Automatically locking QL2.1 hooks with 16 mm diameter

Exchangable hook inserts in diameters 8, 10 and 12 mm

Adjustable, rotatable hook (15° steps) with anti scratch function

Two-component synthetic semi-elliptical rail with anti-scratch function, reduces abrasions on rack

Edge protection and lower mounting for ORTLIEB pannier carrying system



Version black

Height cm/in.	Width cm/in.	Depth cm/in.	Vol. l/cu.in.	Weight g/oz.
42/16,5	23/32 9/12,6	17/6,7	40/2441 (pair)	1900/67.1 (pair)

- Classical rear pannier (pair) with roll closure in colour combination black/black or white/black
- Large ORTLIEB logo print
- QL2.1 system for racks up to 16 mm, adjustable without requiring tools
- Including reduction pieces for tube diameters 8, 10 and 12 mm with anti-scratch function (prevents damage to the rack)
- Material combination of PVC-free PD62 and PS60 (PU)
- Including integrated pocket and shoulder strap
- Lower hook rail made of two-component „hard-soft“ synthetic prevents abrasions on carrier
- Can be used on left or right side (symmetrical shape)
- Can be combined with the ORTLIEB Rack-Pack (size S and M)
- Highly reflective 3M Scotchlite reflectors
- Simultaneous use of ORTLIEB Travel-Biker or Trunk-Bag possible
- Can be easily cleaned inside
- Optional accessories: ORTLIEB pannier carrying system, outer pocket/s (size S), anti-theft device, mesh pocket, bottle cage, QL2.1 hook 20 mm

Panniers come as a pair with shoulder straps, 2 pairs of reduction pieces in 8, 10 and 12 mm

Note: In order to meet standard IP64 (6=dustproof, 4=protected against splash water coming from all directions) the roll closure must be rolled at least 3-4 times.

PRODUCT-INFO

Please find information on IP symbols on our info sheet or at www.ortlieb.com/ip-symbols

BR_BnW_10_2014